

LB-I4R

Item number 23.0100-*

Insulated Ø 4 mm rigid socket. Machined brass. Metal thread jacket on the insulation. The socket can be screw-mounted in predrilled panels. With round nut. Solder connection.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 VAC, 25 A / 60 VDC, 25 A
Colours *	20 21 22 23 24 25 26 27 28 29
Thread	M8x0,5
Test accessory acc. to	IEC EN 61010-031
Component parts	BI-LB-I4R; MU/M8x0,5; SP4