

LB-I4R-A

Item number 23.0180-*

Insulated Ø 4 mm rigid socket. Machined brass. Metal thread jacket on the insulation. The socket can be screw-mounted in predrilled panels. Available with round nut. Flat connecting tab 4.8 mm x 0.8 mm.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 VAC, 25 A / 60 VDC, 25 A
Colours *	
Thread	M8x0,5
Test accessory acc. to	IEC EN 61010-031
Component parts	BI-LB-I4R-A
Supplied assembly material	MUR/M8x0,5; SP4