



LK425-A

Item number 28.0073-*

Highly flexible, with stackable Ø 4 mm MULTILAM plugs on both ends.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 VAC, 32 A / 60 VDC, 32 A
Surface treatment electrical contact	Au
Base material electrical contact	CuZn
Lead cross section	2.5 mm ²
Lead lengths <input type="text"/>	25 cm; 50 cm; 75 cm; 100 cm; 150 cm; 200 cm
Lead insulation	PVC
Colours *	<input type="checkbox"/> 20 <input type="checkbox"/> 21 <input type="checkbox"/> 22 <input type="checkbox"/> 23 <input type="checkbox"/> 24 <input type="checkbox"/> 25 <input type="checkbox"/> 26 <input type="checkbox"/> 27 <input type="checkbox"/> 28 <input type="checkbox"/> 29
Test accessory acc. to	IEC EN 61010-031