


SEB4-G/N-X



Item number 49.7092-*

Insulated, rigid, \varnothing 4 mm, accepting spring-loaded \varnothing 4 mm plugs with rigid insulating sleeve. Machined brass. The socket is pressed into pre-drilled panels of plastic, metal, etc. Connection: Threaded bolt M4 and soldering hole

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT III, 24 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Colours *	20 21 22 23 24 25 27
Test accessory acc. to	IEC EN 61010-2-030
Approvals	UR
Remarks	Accessories: Press-in tool MB4-S