

XEP-S

Item number 66.9681-*

Insulated, rigid, Ø 4 mm, accepting spring-loaded Ø 4 mm plugs with rigid insulating sleeve. The socket is pressed into pre-drilled panels of plastic, metal, etc. Connection: Solder pin Ø 2.0 mm.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT III, 20 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Colours *	21 22 23
Test accessory acc. to	IEC EN 61010-031
Approvals	UR
Remarks	Other color available on request.