

XEP-FS

Item number 66.9685-*

Insulated, rigid, Ø 4 mm, accepting spring-loaded Ø 4 mm plugs with rigid insulating sleeve. The socket is pressed into pre-drilled panels of plastic, metal, etc. Connection: Flat connecting tab 4.8 mm x 0.8 mm.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT III, 20 A
Colours *	21 22 23
Test accessory acc. to	IEC EN 61010-031
Approvals	UR
Remarks	Accessories: Flat connecting receptacles FSH4,8x0,8; Press-in tool MB4-S; Other color available on request.